

COD.	bar	drop	l/min	I/ha (spazio tra gli ugelli: 50 cm) I/ha (nozzle spacing: 50 cm) I/ha (espacio entre las boquillas: 50 cm)							
				6 km/h	8 km/h	10 km/h	12 km/h	14 km/h	16 km/h	18 km/h	20 km/h
TFA11002	2	VC	0.65	131	98	78	65	56	49	44	39
	3	C	0.80	160	120	96	80	69	60	53	48
	4	C	0.92	184	138	110	92	79	69	61	55
	5	M	1.03	206	155	124	103	88	77	69	62
	6	M	1.13	226	170	136	113	97	85	75	68
TFA11003	2	VC	0.98	196	147	118	98	84	73	65	59
	3	VC	1.20	240	180	144	120	103	90	80	72
	4	C	1.39	278	209	167	139	119	104	93	83
	5	C	1.55	310	233	186	155	133	116	103	93
	6	C	1.70	339	255	204	170	145	127	113	102
TFA11004	2	VC	1.31	261	196	157	131	112	98	87	78
	3	VC	1.60	320	240	192	160	137	120	107	96
	4	C	1.85	370	278	222	185	159	139	123	111
	5	C	2.07	414	311	248	207	177	155	138	124
	6	C	2.26	453	339	272	226	194	170	151	136
TFA11005	2	VC	1.63	327	245	196	163	140	122	109	98
	3	VC	2.00	400	300	240	200	171	150	133	120
	4	VC	2.31	462	346	277	231	198	173	154	139
	5	C	2.58	516	387	310	258	221	193	172	155
	6	C	2.83	566	424	339	283	242	212	189	170

DIMENSIONE DELLE GOCCE DROP SIZE RATING DIMENSIONES DE LAS GOTAS	
<b>M</b> <i>Media-Medium-Media</i>	217µm ÷ 353µm
<b>C</b> <i>Grossa-Coarse-Gruesa</i>	354µm ÷ 464µm
<b>VC</b> <i>Molto grossa-Very coarse-Muy gruesa</i>	> 464µm

millesimo di millimetro (Es.: 250µm = 0.25 mm)  
µm= thousandth of millimeter (E.g.: 250µm = 0.25 mm)  
milésimo de milímetro (Ej.: 250µm = 0.25 mm)

