





COD.	 bar	 drop	 l/min	I/ha (spazio tra gli ugelli: 50 cm) I/ha (nozzle spacing: 50 cm) I/ha (espacio entre las boquillas: 50 cm)							
				6 km/h	8 km/h	10 km/h	12 km/h	14 km/h	16 km/h	18 km/h	20 km/h
WRC110015	2	F	0.49	98	73	59	49	42	37	33	29
	3	F	0.60	120	90	72	60	51	45	40	36
	4	F	0.69	139	104	83	69	59	52	46	42
	5	F	0.77	155	116	93	77	66	58	52	46
	6	VF	0.85	170	127	102	85	73	64	57	51
WRC11002	2	F	0.65	131	98	78	65	56	49	44	39
	3	F	0.80	160	120	96	80	69	60	53	48
	4	F	0.92	185	139	111	92	79	69	62	55
	5	F	1.03	207	155	124	103	89	77	69	62
	6	VF	1.13	226	170	136	113	97	85	75	68
WRC110025	2	F	0.82	163	122	98	82	70	61	54	49
	3	F	1.00	200	150	120	100	86	75	67	60
	4	F	1.15	231	173	139	115	99	87	77	69
	5	F	1.29	258	194	155	129	111	97	86	77
	6	F	1.41	283	212	170	141	121	106	94	85
WRC11003	2	F	0.98	196	147	118	98	84	73	65	59
	3	F	1.20	240	180	144	120	103	90	80	72
	4	F	1.39	277	208	166	139	119	104	92	83
	5	F	1.55	310	232	186	155	133	116	103	93
	6	F	1.70	339	255	204	170	145	127	113	102
WRC11004	2	F	1.31	261	196	157	131	112	98	87	78
	3	F	1.60	320	240	192	160	137	120	107	96
	4	F	1.85	370	277	222	185	158	139	123	111
	5	F	2.07	413	310	248	207	177	155	138	124
	6	F	2.26	453	339	272	226	194	170	151	136
WRC11005	2	F	1.63	327	245	196	163	140	122	109	98
	3	F	2.00	400	300	240	200	171	150	133	120
	4	F	2.31	462	346	277	231	198	173	154	139
	5	F	2.58	516	387	310	258	221	194	172	155
	6	F	2.83	566	424	339	283	242	212	189	170
WRC11006	2	M	1.96	392	294	235	196	168	147	131	118
	3	M	2.4	480	360	288	240	206	180	160	144
	4	M	2.77	554	416	333	277	238	208	185	166
	5	M	3.10	620	465	372	310	266	232	207	186
	6	M	3.39	679	509	407	339	291	255	226	204
WRC11008	2	M	2.61	523	392	314	261	224	196	174	157
	3	M	3.20	640	480	384	320	274	240	213	192
	4	M	3.70	739	554	443	370	317	277	246	222
	5	M	4.13	826	620	496	413	354	310	275	248
	6	M	4.53	905	679	543	453	388	339	302	272

	DIMENSIONE DELLE GOCCE DROP SIZE RATING DIMENSIONES DE LAS GOTAS
VF	Molto fine-Very fine-Muy fina < 119µm
F	Fine-Fine-Fina 119µm ÷ 216µm
M	Media-Medium-Media 217µm ÷ 353µm

millesimo di millimetro (Es.: 250µm = 0.25 mm)
µm= thousandth of millimeter (E.g.: 250µm = 0.25 mm)
milésimo de milímetro (Ej.: 250µm = 0.25 mm)